

The STEPDOS pump can be customised for any application.



## Self-priming and maintenance free dosing pump

Javac has released its self-priming, maintenance-free STEPDOS dosing pump.

The microprocessor-controlled diaphragm metering pump is designed for use with neutral and aggressive liquids.

The STEPDOS pump, which can be run dry, produces continuous and precise flow (+/- 2 per cent) at low rpm, which is achieved by means of a stepper motor. This ensures the suction part of the cycle is completed at maximum speed.

However, the output part of the cycle is controlled on a variable basis according to the selected speed. Constant adaptation of the motor speed results in a steady output over the entire cycle.

The pump is enclosed in a compact protective housing (IP65). Javac offers custom solutions for every application.

### ■ Javac

Keith Weir

1300 786 771

[sales@javac.com.au](mailto:sales@javac.com.au)

[www.javac.com.au](http://www.javac.com.au)